

Closed magnetic-coupled circulation pump with integrated overload protection. Housing of stainless steel with 2 handles. Operation either manual (on/off) or external via 3-line-connector. Control cable (option) for the potential free contact of Unistat Tango and the big power Unistats, all Compatible Control Thermostats and Unichillers.

Technical data according to DIN 12876

Operating temperature range	-120...350 °C
Circulation pump	MK pump
max. delivery of pressure pump	110 l/min
max. delivery pressure	2 bar
Delivery at 0,5 bar	94 l/min
Delivery at 1,0 bar	79 l/min
Delivery at 1,5 bar	59 l/min
Pump connection	M38x1,5 male
Overall dimensions WxDxH **	275x420x295 mm
Net weight	27 kg
Geräuschpegel	65 dB(A)
Power supply (3 Phase)	380-480V 3~ 50/60Hz
max. current (3 Phase)	2,5 A
Fuse (3 phase)	3x4 A
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C



Order-No.: 1086.0001.00

from Serial-No.:	417309	1.0/21
------------------	--------	--------

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:
bridge plug #6478

Optional accessories:
control cable #6221, temperature control / - connection hoses, adapters, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

** Please respect space requirements. See operating conditions at www.huber-online.com