

Technical data

Operating temperature range	-90...230 °C
Operating temperature	20 °C
Material	stainless steel 1.4404, 1.4571
Sealing material	Special material, PTFE
Nennweite	20 mm
Connection	M30x1,5 male
Location	hose side
Max. pressure at 20°C	25 bar
Leakage rate *	<0,4 ml per decoupling cycle
Cv value *	14

**Order-No.: 10406****1.0/18**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Optional accessories:

Verschlusskupplung #10407, Druckentlastungseinrichtung #10417, Winkelanschluss 90° #10450, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Bore shape Y (60°) to DIN 3863, piping/temperature hoses: Connectors to DIN 3863

* Measured with water (20 °C) at an ambient temperature of 20 °C.

Note:

When using ethanol as thermofluid: min. working temperature limit -60 °C.