

Refrigerated Heating Circulator with air-cooled refrigerating unit. Powerful, variable speed pump, housing of stainless steel, CFC and H-CFC free. Speed controlled pump (soft start), pump pressure control.

With adjustable overtemperature protection according to DIN 12876.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

Further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

4-year warranty - registration required.

Please note:

The machine is developed exclusively for external open operation, and does not possess an expansion tank. The filling of the thermofluid, and allowance for the temperature dependent volume changes is only possible via an externally connected application.

Technical data according to DIN 12876

Operating temperature range	-40...200 °C
Temperature stability at -10°C	0,01 K
temperature set point / display	5,7" colour Touchscreen
Resolution of display	0,01 K
Internal temperature sensor	Pt100
Sensor external connection	Pt100
Interface digital	Ethernet, USB (Host u. Device), RS232
digital input	ECS ONE
digital output	POKO ONE
Alarm message	optic, acoustic, relay
Safety classification	III / FL
Heating power	1,5 kW
Cooling power with	Thermooil
at 200°C	0,6 kW
at 150°C	0,6 kW
at 100°C	0,6 kW
at 50°C	0,6 kW
at 20°C	0,6 kW
Cooling power with	Ethanol
at 0°C	0,6 kW
at -20°C	0,35 kW
at -30°C	0,2 kW
at -40°C	0,04 kW
Refrigeration machine	air-cooled, natural refrigerant
Refrigerant (ASHRAE, GHS)	R-290 (A3, H220)
Global Warming Potential (GWP)	0,02
Refrigerant quantity	0,099 kg
Circulation pump:	
max. delivery	47 l/min
max. delivery pressure	0,9 bar
Pump connection	M24x1,5 male



Order-No.: 1041.0005.01

Technical data according to DIN 12876

max. permissible kin. viscosity	50 mm ² /s
min. filling capacity	1,5 l
Overall dimensions WxDxH **	295x530x570 mm
Net weight	53 kg
Power supply requirement	110-120V 1~ 60Hz
max. current	15 A
Fuse	16 A
Pressure equipment category	Art. 4.3 PED
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

from Serial-No.:

1.1/20

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini-USB cable #54949, E-grade "Professional" #9496, Adaptor M16x1 male to M24x1,5 female,

Optional accessories:

E-grade "Explore" #10495, external sensor, temperature control / - connection hoses, thermofluids, SpyLight-Software, Com.G@te, further accessories, etc.: see catalog.

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com