

## Technical data

|                             |                         |                         |
|-----------------------------|-------------------------|-------------------------|
| Operating temperature range | -40...140 °C            |                         |
| Material                    | stainless steel, 1.4404 |                         |
| Seal                        | NBR                     | <b>Order-No.: 10816</b> |
| Braiding                    | Yes                     |                         |
| Label*                      | Yes                     |                         |
| Nominal width (DN)          | 25 mm                   |                         |
| Length                      | 300 cm                  |                         |
| Net weight                  | 4 kg                    |                         |
| Connection                  | G1                      |                         |
| Max. pressure at 20°C       | 10 bar                  |                         |
| Test pressure               | 1,25 bar                |                         |
| Min. bending radius         | 220 mm                  |                         |
| Fire rating                 | UL94-HB                 |                         |

**1.0/19**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: sleeve nut made of nickel-plated brass.

\*Label: stamp on band: Order No., -40 °C...140 °C, PS 10 bar, KW/year