

Refrigerated Heating Circulator with water-cooled cooling machine and optical level indicator. Magnetic coupled circulation pump made of stainless steel. Automatical switch-over and capacity adaption for heating and cooling machine. Copper soldered evaporator, moistened parts and housing made of stainless steel. As well as for externally closed and also externally open applications. With adjustable overtemperature protection according to DIN 12876. Powerful variable speed pump (soft start) with integrated pressure control with optional external pressure sensor.

Unistat „P“ Models: Circulating pumps with a high discharge pressure for applications with high pressure drops, e.g. in the Flow-Through chemistry or in the Semicon industry.

Pilot ONE:

The Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, ZH, PT, JA, CS, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

Further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

4-year warranty - registration required.

- the required voltage is provided using a stand alone transformer (supplied as standard)

Technical data according to DIN 12876

Operating temperature range	-90...200 °C
Temperature stability at -10°C	0,01 K
temperature set point / display	5,7" colour Touchscreen
Resolution of display	0,01 K
Internal temperature sensor	Pt100
Sensor external connection	Pt100
Interface digital	Ethernet, USB (Host u. Device), RS232
digital input	ECS ONE
digital output	POKO ONE
Alarm message	optic, acoustic, relay
Safety classification	III / FL
Heating power	24 kW
Cooling power with	Thermooil
at 200°C	19 kW
at 100°C	19 kW
at 20°C	19 kW
Cooling power with	Ethanol
at 0°C	20 kW
at -20°C	20 kW
at -40°C	20 kW
at -60°C	15 kW
at -80°C	5 kW
Refrigeration machine	water-cooled, CFC- and HCFC-free
Refrigerant (ASHRAE, GHS)	R-452A (A1, H280)
Global Warming Potential (GWP)	2141
Refrigerant 2nd stage (ASHRAE, GHS)	R-23 (A1, H280)
Global Warming Potential (GWP)	14800
Refrigerant quantity 2nd stage	2,44 kg
CO2 equivalent 2nd stage	36,1 t
UN-number	UN 2857



Order-No.: 1082.0005.01

Technical data according to DIN 12876

Circulation pump:	MK pump
max. delivery	191 l/min
max. delivery pressure	5,5 bar
Delivery at 1,0 bar	167 l/min
Delivery at 2,0 bar	140 l/min
Delivery at 3,0 bar	107 l/min
Delivery at 4,0 bar	67 l/min
Delivery at 5,0 bar	22 l/min
Pump connection	M38x1,5 male
max. permissible kin. viscosity	50 mm ² /s
Cooling water connection	G3/4 male
Consumption at water 15°C, flow 0°C	1300 l/h
min. cooling water differential pressure	1 bar
max. cooling water pressure	6 bar
min. filling capacity	12 l
Filling capacity expansion tank	29 l
Overall dimensions WxDxH **	950xx mm
Abmessungen Temperiergerät BxTxH	x1205x1650 mm
Gesamtgewicht, netto	1546 kg
Gewicht Trafo	650 kg
Power supply factory configured (3 Phase)	208V 3~ 60Hz
Input Voltage transformer	208V 3~ 60HZ
Output voltage transformer	440V 3~ 60HZ
max. Stromaufnahme Temperiergerät mit Trafo	270 A
Absicherung für Eingangsspannung Trafo	3X300 A
Pressure equipment category	I
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

from Serial-No.:

1.1/24

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini-USB cable #54949, E-grade "Professional" #9496, hose connection for G3/4 male,

Optional accessories:

E-grade "Explore" #10495, SpyLight-Software, Com.G@te Namur, PC-Com.G@te-cable, Holder for Com.G@te #10018, Com.G@te-extension cable: upon request, RS232 adapter cable #55018, Thermofluid, external pressure sensor, metal hoses, braided hoses for cooling water, external sensor, connecting cable, isolation sleeve for external open applications, float switch in sight glass for extended security, further accessories, etc.: see catalog.

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 1 bar differential pressure between cooling water inlet and - outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materials used in the cooling water circuit include; copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and +2% frequency -> not allowed!

-5% voltage and -2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Attention: leakage current > 3,5mA

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

External branch circuit protection according to UL 489 required.

For the specification, please refer to the electrical schematics.

Technical data according to DIN 12876

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

* * Please respect space requirements. See operating conditions at www.huber-online.com