

External pressure pump. Bearing out of the liquid circuit. All parts in the liquid circuit and housing made of stainless steel. Operation either manual (on/off) or external via 3-line-connector. Cable (Option) for the potential free contact of Unistat Tango and the big power Unistats, all Compatible Control Thermostats and Unichillers.

**Technical data according to DIN 12876**

Operating temperature range	-120...300 °C
Circulation pump	Yes
max. delivery of pressure pump	55 l/min
max. delivery pressure	1 bar
Delivery at 0,25 bar	45 l/min
Delivery at 0,5 bar	34 l/min
Delivery at 0,75 bar	20 l/min
Pump connection	M24x1,5 male
Overall dimensions WxDxH **	219x390x214 mm
Net weight	10 kg
Geräuschpegel	50 dB(A)
Power supply requirement	208-240V 1~/2~ 50/60Hz
max. current	1 A
Fuse	2 A
min. ambient temperature	5 °C
max. ambient temperature	32 °C

**Order-No.: 1085.0001.00****from Serial-No.:****419357****1.0/21**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.