

Technical data

Operating temperature range	-90...200 °C	
Material	stainless steel, 1.4404	
Braiding	Yes	Order-No.: 10867
Label*	Yes	
Nominal width (DN)	40 mm	
Length	100 cm	
Net weight	9,4 kg	
Connection 1	Flange EN1092-1 type 11	
Connection 2	Flange EN1092-1 type 02, type 33	
Max. pressure at 20°C	10 bar	
Test pressure	1,25 bar	
Min. bending radius	260 mm	
Fire rating	UL94-HB	

1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mounting kit with 8x bolts, nuts and spring washers, as well as 2 pieces of graphite seals

Insulation: Special insulation with additional smooth silicon hose, ends covered with silicon caps.

*Label: stamp on band: Order No., -90 °C...200 °C, PS 10 bar, KW/year