

Closed magnetic-coupled circulation pump with integrated overload protection. Housing of stainless steel with 2 handles. Operation either manual (on/off) or external via 3-line-connector. Control cable (option) for the potential free contact of Unistat Tango and the big power Unistats, all Compatible Control Thermostats and Unichillers.

## Technical data according to DIN 12876

|                                |                     |
|--------------------------------|---------------------|
| Operating temperature range    | -120...350 °C       |
| Circulation pump               | MK pump             |
| max. delivery of pressure pump | 120 l/min           |
| max. delivery pressure         | 4 bar               |
| Delivery at 1,0 bar            | 85 l/min            |
| Delivery at 2,0 bar            | 54 l/min            |
| Delivery at 3,0 bar            | 27 l/min            |
| Pump connection                | M38x1,5 male        |
| Overall dimensions WxDxH **    | 275x420x295 mm      |
| Net weight                     | 27 kg               |
| Geräuschpegel                  | 71 dB(A)            |
| Power supply (3 Phase)         | 380-480V 3~ 50/60Hz |
| max. current (3 Phase)         | 2,5 A               |
| Fuse (3 phase)                 | 3x4A                |
| Degree of Protection           | IP20                |
| min. ambient temperature       | 5 °C                |
| max. ambient temperature       | 40 °C               |



Order-No.: 1087.0001.00

|                  |        |        |
|------------------|--------|--------|
| from Serial-No.: | 417303 | 1.0/21 |
|------------------|--------|--------|

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:  
bridge plug #6478

Optional accessories:  
control cable #6221, temperature control / - connection hoses, adapters, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20 °C

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)