

Refrigerated Heating Circulator with the state of the art Peltier technology, i.e. Free of refrigerants and therefore completely environmentally friendly. Extremely quiet in operation, minimal space requirement. Powerful Pressure pump made of industrial plastic material. Temperature range up to max. 70°C.

NEW: OLÉ controller:

OLÉ combines state-of-the-art technology with simple operation. Models with OLÉ controller are suitable for routine tasks in research and industry and are convincing as practice oriented basic equipment:

- * Large, bright OLED display
- * Simple operation with menu navigation
- * Simultaneous display of set point, internal temperature, Tmin and Tmax
- * USB (Device) and RS232 interfaces
- * Autostart function for power failure

4-year warranty - registration required.

Technical data according to DIN 12876

Operating temperature range	4...70 °C
temperature set point / display	digital
Resolution of display	0,1 K
Interface digital	USB (Device), RS232
Alarm message	Interface
Temperature stability at 15°C	optic, acoustic
Safety classification	0,2 K
Cooling power with	I / NFL
at 20°C	water, water-glycol mixture
at 10°C	0,28 kW
at 4°C	0,1 kW
heating capacity with	0,03 kW
at 70°C	water, water-glycol mixture
at 40°C	0,1 kW
at 20°C	0,42 kW
at 10°C	0,62 kW
at 4°C	0,67 kW
Circulation pump	0,7 kW
max. delivery	Pressure pump
max. delivery pressure	1,85 l/min
Pump connection	0,95 bar
min. filling capacity	Connector with hose barb
max. filling capacity	0,1 l
min. filling capacity cooling circuit (internal)	0,22 l
max. filling capacity cooling circuit (internal)	0,1 l
Overall dimensions WxDxH **	0,2 l
Net weight	215x310x312 mm
sound pressure level +/- 4 dB(A)	13 kg
Power supply requirement	60 dB(A)
max. current	100-240V 1~/2~ 50/60Hz
min. Fuse	4,5 A
max. Fuse	10A
Pressure equipment category	16A
Degree of Protection	Art. 4.3 PED
min. ambient temperature	IP20
max. ambient temperature	5 °C
	40 °C



Order-No.: 3044.0002.98

from Serial-No.: 430097

1.1/21

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

Connector with hose barb #63795

Optional accessories:

Technical data according to DIN 12876

temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

** Please respect space requirements. See operating conditions at www.huber-online.com