

Chiller with air-cooled refrigerating unit and circulation pump. Evaporator (cooler), tank and housing of stainless steel. Pump made of industrial plastic material. Digital Temperature adjustment and digital temperature display. Adjustable bypass. Level indicator with sight glass.

Unichiller „P“ Models: Circulating pumps with a high discharge pressure for applications with high pressure drops.

#### Pilot ONE:

The Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, ZH, PT, JA, CS, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

#### Technical data according to DIN 12876

Operating temperature range	-10...40 °C	<b>Order-No.: 3052.0023.01</b>
temperature set point / display	5,7" colour Touchscreen	
Internal temperature sensor	Pt100	
Sensor external connection	Pt100	
Temperature stability at -10°C	0,5 K	
Interface digital	Ethernet, USB (Host u. Device), RS232	
Safety classification	I / NFL	
Cooling power at ambient temperature +20°C	.	
at 15°C	2,5 kW	
at 0°C	2 kW	
at -10°C	1,2 kW	
Refrigeration machine	air-cooled, CFC- and HCFC-free	
Refrigerant (ASHRAE, GHS)	R-449A (A1, H280)	
Global Warming Potential (GWP)	1397	
Refrigerant quantity	0,5 kg	
CO2 equivalent	0,7 t	
Circulation pump:	B	
max. delivery	25 l/min	
max. delivery pressure	2,5 bar	
Delivery at 0,5 bar	21 l/min	
Delivery at 1,0 bar	17 l/min	
Delivery at 1,5 bar	11 l/min	
Delivery at 2,0 bar	6 l/min	
Pump connection	G3/4 male	
min. filling capacity	3,8 l	
Volume of expansion	1,7 l	
Overall dimensions WxDxH **	460x590x743 mm	
Net weight	81 kg	
sound pressure level +/- 4 dB(A)	64 dB(A)	
Power supply requirement	220-240V 1~/2~ 50Hz	
max. current	10,5 A	

## Technical data according to DIN 12876

Fuse	16 A
Pressure equipment category	Art. 4.3 PED
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

<b>from Serial-No.:</b>	<b>510779</b>	<b>1.1/22</b>
-------------------------	---------------	---------------

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Included Accessories:

mini-USB cable #54949, cover expansion vessel, Hose coupling for G3/4 male,

### Optional accessories:

Com.G@te, external sensor, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

### Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer).

It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

### Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)