

Chiller with water-cooled refrigerating unit and circulation pump. Evaporator (cooler), tank and housing of stainless steel. Pressure-suction pump made of industrial plastic material. Digital Temperature adjustment and digital temperature display. Level indicator with sight glass. With adjustable overtemperature protection according to DIN 12876.

## Pilot ONE:

The Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, ZH, PT, JA, CS, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

## switch for whisper mode:

Reduced sound pressure level: 51 dB(A): +/- 4 dB(A)

## Pump data for whisper mode:

Delivery rate: 14 l/min

Delivery pressure: 0.2 bar

Delivery rate (suction): 11 l/min

Delivery pressure (suction): 0.18 bar

## Technical data according to DIN 12876

|  |                                       |                                |
|--|---------------------------------------|--------------------------------|
| Operating temperature range                | -20...100 °C                          |                                |
| temperature set point / display            | 5,7" colour Touchscreen               |                                |
| Internal temperature sensor                | Pt100                                 | <b>Order-No.: 3080.0012.01</b> |
| Sensor external connection                 | Pt100                                 |                                |
| Temperature stability at -10°C             | 0,2 K                                 |                                |
| Interface digital                          | Ethernet, USB (Host u. Device), RS232 |                                |
| Safety classification                      | III / FL                              |                                |
| Heating power at 240V                      | 2,1 kW                                |                                |
| Heating power at 230V                      | 2 kW                                  |                                |
| Heating power at 220V                      | 1,8 kW                                |                                |
| Heating power at 208V                      | 1,6 kW                                |                                |
| Cooling power at ambient temperature +20°C |                                       |                                |
| at 15°C                                    | 1 kW                                  |                                |
| at 0°C                                     | 0,8 kW                                |                                |
| at -10°C                                   | 0,55 kW                               |                                |
| at -20°C                                   | 0,35 kW                               |                                |
| Refrigeration machine                      | water-cooled, natural refrigerant     |                                |
| Refrigerant (ASHRAE, GHS)                  | R-290 (A3, H220)                      |                                |
| Global Warming Potential (GWP)             | 0,02                                  |                                |
| Refrigerant quantity                       | 0,07 kg                               |                                |
| Circulation pump                           | Pressure- and suction pump            |                                |
| max. delivery                              | 24 l/min                              |                                |
| max. delivery pressure                     | 0,7 bar                               |                                |
| max. delivery (suction)                    | 18 l/min                              |                                |

## Technical data according to DIN 12876

|  |                        |
|--|------------------------|
| max. delivery pressure (suction)         | 0,4 bar                |
| Pump connection                          | M16x1 male             |
| Cooling water connection                 | G1/2 male              |
| min. cooling water differential pressure | 3 bar                  |
| max. cooling water pressure              | 6 bar                  |
| min. filling capacity                    | 2,8 l                  |
| Volume of expansion                      | 2,2 l                  |
| Overall dimensions WxDxH **              | 280x490x424 mm         |
| Net weight                               | 40 kg                  |
| Power supply requirement                 | 208-240V 1~/2~ 50/60Hz |
| max. current                             | 12 A                   |
| Fuse                                     | 16 A                   |
| Pressure equipment category              | Art. 4.3 PED           |
| Degree of Protection                     | IP20                   |
| min. ambient temperature                 | 5 °C                   |
| max. ambient temperature                 | 40 °C                  |

**from Serial-No.:** **574334** **1.1/24**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Included Accessories:

mini-USB cable #54949, hose connection NW12 #6087, sleeve nuts thread M16x1 #6089, blank plug #6088, cover expansion vessel #25178 hose coupling cooling water for G1/2 male

### Optional accessories:

Com.G@te, external sensor, Drain valve, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 3 bar differential pressure between cooling water inlet and - outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materials used in the cooling water circuit include: copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

### Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer).

It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

### Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)