

Technical data

Operating temperature range	-60...260 °C
Material	industrial plastic material hose
Braiding	Yes
Label*	Yes
Nominal width (DN)	12 mm
Length	100 cm
Net weight	1 kg
Connection	M24x1,5 female mit Isolation
Outer covering	
Outside diameter	37 mm
Max. pressure at 20°C	6 bar
Test pressure	1,25 bar
Min. bending radius	150 mm
Fire rating	UL94-HB

**Order-No.: 9325****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

*Label: stamp on band: Order No., -60 °C...260 °C, PS 6 bar, KW/year