

Technical data

Operating temperature range	-50...200 °C
Material	stainless steel, 1.4404
Braiding	no
Label*	Yes
Nominal width (DN)	12 mm
Length	300 cm
Net weight	1,95 kg
Connection	M16x1
Outside diameter	33 mm
Max. pressure at 20°C	6 bar
Test pressure	1,25 bar
Min. bending radius	120 mm
Fire rating	UL94-HB

**Order-No.: 9611****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

*Label: stamp on band: Order No., -50 °C...200 °C, PS 6 bar, KW/year