

Chiller with air-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open tank and copper soldered evaporator made of stainless steel. With digital level indicator. Condenser in air-cooled design, performance-optimized by a built-in high-efficiency fan motor. Powerful feed pump with integrated overtemperature protection. The flow rate can be adjusted via the manual bypass valve on the backside of the chiller.

Control unit B400 / RB400:

Capacitive operating interface with OLED display and multi-coloured status notification for instant identification of the current operating status. Choice of eight different system languages (DE, EN, ES, FR, IT, PT, RU, TR). Separate operating option for the feed pump and the cooling unit with convenient adjustment of the desired setpoint. Operating of the system can be evaluated on a PC or notebook via an integrated RS232 interface.

Technical data according to DIN 12876

Operating temperature range	-20...15 °C
temperature set point / display	colour LED Touchscreen
Internal temperature sensor	Pt100
Temperature stability at -10°C	1,5 K
Interface digital	RS232
Safety classification	I / NFL
Cooling power at ambient temperature 20°C	.
at 15°C	4 kW
at 10°C	3,5 kW
at 0°C	2,1 kW
at -10°C	2 kW
at -20°C	0,8 kW
Refrigeration machine	air-cooled, CFC- and HCFC-free
Refrigerant (ASHRAE, GHS)	R-449A (A1, H280)
Refrigerant quantity	1,6 kg
Circulation pump:	
max. delivery	30 l/min
max. delivery pressure	4 bar
Pump connection	G1/2 male
min. filling capacity	10 l
max. filling capacity	11 l
Overall dimensions WxDxH **	580x660x820 mm
Net weight	135 kg
sound pressure level +/- 4 dB(A)	62 dB(A)
Power supply requirement	208V 2~ 60Hz
max. current	19 A
Fuse	2x20 A
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C



Order-No.: VDH1101336

from Serial-No.:

1.0/20

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

2pcs Hose nozzles Ø8 mm, bath cover, Bypass valve

Optional accessories:

overpressure Bypass valve, drain valve, RS232 cable, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and +2% frequency -> not allowed!

-5% voltage and -2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Technical data according to DIN 12876

Recommended thermofluid: Water - Monoethylene Glycol 50:50

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com