

Instant water heater with housing, atmospheric open tank and heating module made of stainless steel. With digital level indicator. Powerful feed pump with integrated overtemperature protection. Optional the flow rate could be adjusted via the manual bypass valve on the backside of the heater.

Control unit B400 / RB400:

Capacitive operating interface with OLED display and multi-coloured status notification for instant identification of the current operating status. Choice of eight different system languages (DE, EN, ES, FR, IT, PT, RU, TR). Separate operating option for the feed pump and the cooling unit with convenient adjustment of the desired setpoint.

Technical data according to DIN 12876

Operating temperature range	35...85 °C
temperature set point / display	colour LED Touchscreen
Internal temperature sensor	Pt100
Temperature stability at 30°C	+/-0,1 K
Safety classification	I / NFL
Heating power	12 kW
Circulation pump:	
max. delivery	87 l/min
max. delivery pressure	3,7 bar
Pump connection	G3/4 male
min. filling capacity	24 l
max. filling capacity	27 l
Overall dimensions WxDxH **	580x900x830 mm
Net weight	130 kg
Power supply (3 Phase)	460V 3~ 60Hz
max. current (3 Phase)	20 A
Fuse (3 phase)	3x25A
Degree of Protection	IP20



Order-No.: VDH33100025

from Serial-No.:	215224	1.0/24
-------------------------	---------------	---------------

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.